



Pushing Performance
Since 1945

har-light



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 453 2401
Specification	har-light
HARTING eCatalogue	https://b2b.harting.com/09454532401

Identification

Category	Operator interfaces
Series	har-light
Element	Pilot light buttons

Version

Diameter of the mounting hole	30.5 mm
Details	This item requires additional contact blocks, a module holder, and a protective calotte. Please select these under “Matching Products”.

Technical characteristics

Overvoltage category	III (protection by low voltage)
Tightening torque	≤2.5 Nm Fixing nut
Operating temperature	-40 ... +70 °C
Storage temperature	-50 ... +85 °C
Degree of protection acc. to IEC 60529	IP65
Isolation group	I (600 ≤ CTI)
Thickness of the panel	1 ... 8 mm

Material properties

Colour	anthracite
--------	------------

Specifications and approvals

Specifications	EN 60947-5-1
----------------	--------------



Pushing Performance
Since 1945

Specifications and approvals

UL / CSA	UL 60947-5-1 NKCR.E534795
	CSA C22.2 No. 60947-5-1:22 NKCR7.E534795
	UL 60947-1 NKCR.E534795
	CSA C22.2 No. 60947-1:22 NKCR7.E534795

Commercial data

Packaging size	10
Net weight	21.5 g
Country of origin	Germany
European customs tariff number	85318070
GTIN	5713140449794
ETIM	EC000221
eCl@ss	27371211 Front element for warning lights