
Multilayer Ceramic Chip Capacitors

C4532C0G2E333J200KA

Product Status	Production
TDK Item Description	C4532C0G2E333JT****
Applications	Commercial Grade Please refer to Part No. CGA8M3C0G2E333J200KA for Automotive use.
Feature	MidMid Voltage (100 to 630V)
Series	C4532 [EIA 1812]
Brand	TDK
Environmental Compliance	RoHS, REACH, Halogen Free, Lead Free



Size	
Length(L)	4.50mm ±0.40mm
Width(W)	3.20mm ±0.40mm
Thickness(T)	2.00mm ±0.20mm
Terminal Width(B)	0.20mm Min.
Recommended Land Pattern (PA)	3.10mm to 3.70mm
Recommended Land Pattern (PB)	1.20mm to 1.40mm
Recommended Land Pattern (PC)	2.40mm to 3.20mm

Electrical Characteristics	
Capacitance	33nF ±5%
Rated Voltage	250VDC
Temperature Characteristic	C0G(0±30ppm/°C)
Q (Min.)	1000
Insulation Resistance (Min.)	10000MΩ
Allowable Voltage	
Allowable Current	


Other	
Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [180mm Reel]
Package Quantity	1000pcs
FIT (Failure In Time)	This will be displayed when you login to myTDK

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.

Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)

Impedance




C4532C0G2E333J200KA

ESR




C4532C0G2E333J200KA

Capacitance




C4532C0G2E333J200KA

DC Bias Characteristic




C4532C0G2E333J200KA

Temperature Characteristic



C4532C0G2E333J200KA(No Bias) C4532C0G2E333J200KA(DC Bias = 125V)

Ripple Temperature Rising




C4532C0G2E333J200KA(85kHz) C4532C0G2E333J200KA(100kHz) C4532C0G2E333J200KA(300kHz)

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.


Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)

Max. Allowable Voltage



C4532C0G2E333J200KA

Max. Allowable Current



C4532C0G2E333J200KA

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.

Multilayer Ceramic Chip Capacitors

C4532C0G2E333J200KA

Associated Images

Land Pattern (Terminal Connection)



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.