Specifications



Eaton QBGFT1015

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,15A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,#14–10 Cu, #12–10 Al,QBGF

General specifications	
PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1015
UPC	786680130953
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
PRODUCT TYPE	GFCI circuit breakers

Downloaded from Arrow.com.

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al

Performance Ratings

AMPERAGE RATING	15 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Miscellaneous

SPECIAL FEATURES	5 mA Trip Sensitivity

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT1015

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.