Part Number : 1301550160
Product Description : Watertite Extreme Connector with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 50A/250V/3ø, Cord Grip Body Size F5
Series Number : 130155
Status : Active
Product Category : Wiring Devices
Engineering Part Number : CS83W64



Documents and Resources

Drawings

1301550160_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130155
Description	Watertite Extreme Connector with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 50A/250V/3ø, Cord Grip Body Size F5
IP Rating	IP67
NEMA Configuration	Non-NEMA Locking CA
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678801472

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	50.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F5 1 1/4"
Cord Type	N/A
Flange	No

Downloaded from Arrow.com.

Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	661.790/g
Poles	3-pole/4-wire
Receptacle Type	Single

Downloaded from Arrow.com.