



Stainless Steel Circular Butting Twin U Die, 500 kcmil, Brown, Index 20

By Burndy
Catalog # [U34RT](#)

12T U Die, 500 kcmil, Brown, Index 20



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin U Style
- Color Code: Brown
- Die Index 20

Application

Crimping

Specifications

Standards - RoHS Compliance Status	EX
Buy American Compliant	No
EU RoHS Indicator	Yes

Conductor

Crimping Ranges	500 Kcmil
-----------------	-----------

Dimensions

Dimension - Width mm	25
Dimension - Width inch	1
Weight	0.37 lb.

Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	<ul style="list-style-type: none"> • Use with Y35, Y750, PAT750 • Y46 and PAT46 with PUADP1 Adapter
Color Code	Brown
Sub Brand	U-DIE
Die Index	20
Die Type	U Die
UPC	781810627419
Type	Die
Construction Material - Main Material	Stainless Steel
UPC 12 Digit	781810627419
UPC 14 Digit GTIN	00781810627419

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)