



Part Number : [152670472](#)

Product Description : 1.00mm Pitch Premo-Flex FFC


Jumper, Opposite Side Contacts (Type D), 102.00mm

Cable Length, Tin (Sn) Plating, 30 Circuits

Series Number : 15267

Status : Active

Product Category : Flat-Flexible Cable (FFC)



Documents & Resources

Drawings

[152670472_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-15267-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15267
Description	1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 102.00mm Cable Length, Tin (Sn) Plating, 30 Circuits
Comments	Contacts on opposite sides, Type D
Product Name	Premo-Flex FFC Jumper
UPC	884982446540

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	60V AC

Physical

Cable Length	102.00mm
Circuits (Loaded)	30
Contact Layout Type	D (opposite side)
Design Feature	Flexible
Flammability	94V-0

Material - Plating Mating	Tin
Net Weight	2.292/g
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40° to +105°C
Termination Style	FFC Connector
Wire/Cable Type	Flat Flex Cable
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Bottom Contact, 3.00mm Height, 30 Circuits, Tin-Bismuth Plating	<u>522713079</u>
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 30 Circuits, Tin-Bismuth Plating	<u>526103071</u>
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 30 Circuits, Tin-Bismuth Plating, with Pick-and-Place Tape	<u>526103075</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, 30 Circuits	<u>528083070</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, with Pick-and-Place Polyimide Tape, 30 Circuits	<u>528083071</u>
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Top Contact, 2.70mm Height, 30 Circuits, Tin-Bismuth Plating	<u>522073085</u>

1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Right-Angle, Non-ZIF, Top Contact Style, 30 Circuits	<u>527933070</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Vertical, Surface Mount Compatible, Non-ZIF, Kinked PC Tails, 30 Circuits	<u>528063010</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 30 Circuits	<u>528073010</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Right-Angle, Non-ZIF, Bottom Contact Style, 30 Circuits	<u>528523070</u>

This document was generated on Sep 22, 2025