

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301020258](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Safeway® Phenolic Hand Lamp with 100W Screw Release Guard with Reflector and Side Outlet, Cord Type 16/3 SJTOW, Cord Length 15.24m (50.0')



**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

|                             |                            |
|-----------------------------|----------------------------|
| <b>Agency Certification</b> |                            |
| CSA                         | LR85374                    |
| <b>General</b>              |                            |
| Product Family              | Portable Lighting          |
| Series                      | <a href="#">130102</a>     |
| NEMA Configuration          | NEMA 5-15                  |
| Outlet                      | Side                       |
| Overview                    | <a href="#">Hand Lamps</a> |
| Product Literature Order No | 987650-8053                |
| Product Name                | Safety Yellow®             |
| Type                        | Hand Lamps                 |
| UPC                         | 78678879529                |
| Woodhead                    | Yes                        |
| <b>Physical</b>             |                            |
| Cord Length - Primary       | 15.24m (50.0')             |
| Cord Length - Secondary     | N/A                        |
| Depth                       | 101.60mm (4.000")          |
| Duty                        | Commercial                 |
| Guard Included              | No                         |
| Guard Type                  | Metal Wire                 |
| Height                      | 381.00mm (15.000")         |
| Length                      | N/A                        |
| Material - Guard            | #8 Gauge Zinc-plated Steel |
| Mounting Style              | Hand Held                  |
| Packaging Type              | Carton                     |
| Socket Construction         | N/A                        |
| <b>Electrical</b>           |                            |
| Bulb Type                   | Incandescent               |
| Cord Type - Primary         | 16/3 SJTOW                 |
| Lamp Type                   | A21                        |
| Lamp Wattage - Maximum      | 100W                       |
| Lumens                      | 1000                       |
| On/Off Switch               | No                         |
| Voltage (Fixture) - Maximum | 240V                       |
| <b>Material Info</b>        |                            |
| Old Part Number             | 271UB163                   |

**EU ELV**  
**Not Reviewed**

|                                                                                                                                           |                   |
|-------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| <b>EU RoHS</b><br><b>Not Reviewed</b><br><b>REACH SVHC</b><br>Not Reviewed<br><b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b> | <b>China RoHS</b> |
|-------------------------------------------------------------------------------------------------------------------------------------------|-------------------|

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

|            |              |
|------------|--------------|
| China ROHS | Not Reviewed |
| ELV        | Not Reviewed |

**Search Parts in this Series**  
[130102](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION