



Part Number : [532591329](#)
Product Description : Mighty-SPOX Header,
3.50mm Pitch, Right-Angle, 13 Circuits, Brass
(CuZn) Contact
Series Number : 53259
Status : Obsolete
Product Category : PCB Headers and
Receptacles



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	53259
Description	Mighty-SPOX Header, 3.50mm Pitch, Right-Angle, 13 Circuits, Brass (CuZn) Contact
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	Mighty-SPOX
UPC	822348135486

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	5.5A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	13
Circuits (maximum)	13
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3536.500/mg
Number of Rows	1
Orientation	Right Angle

Packaging Type	Tray
PC Tail Length	3.50mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	3.50mm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

This document was generated on Mar 08, 2025