Part Number : 190250008
Product Description : Avikrimp Quick Disconnect, Male, for 16-14 AWG (2.00-1.30mm²) Wire, 4.75 x 0.51mm Tab, Carton
Series Number : 19025
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : MCT-57



Documents and Resources

Drawings

190250008_sd.pdf

190250008_stp.zip

Specifications

PS-19902-013-001.pdf

PS-19902-014-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19025
Description	Avikrimp Quick Disconnect, Male, for 16-14 AWG (2.00-1.30mm^2) Wire, 4.75 x 0.51mm Tab, Carton
Comments	Funnel Ferrule Entry
Product Name	Avikrimp
Type	Standard Quick Disconnect
UPC	800753040519

Agency

CSA	LR18689

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Male
Glow-Wire Capable	No
Insulated	Partial
Insulation	Nylon (PA)

Downloaded from Arrow.com.

Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Zinc Chromate
Material - Plating Termination	Zinc Chromate
Material - Resin	Nylon
Net Weight	0.913/g
Orientation	Straight
Packaging Type	Carton
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	4.75mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	4.30mm max.
Wire Size (AWG)	14, 16
Wire Size mm^2	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm^2 (Rings, Spades, Hooks, Block Spades and Flanged Spades)	640010100
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our	640160036

Downloaded from Arrow.com.

PremiumGrade Tool	

This document was generated on Jun 07, 2026

Downloaded from Arrow.com.