

Home >

Series: **Micro-Con-X** refresh

Connector Type:

Coupling Style:

Contact Number:
contact arrangement

Contact Size: ⓘ only one option available

Contact Style:

Contact Gender:

Contact Plating: ⓘ only one option available

Rear Style: ⓘ only one option available

Insert Material: ⓘ only one option available

Color Option: ⓘ only one option available

Wing Option: ⓘ only one option available

Downloads:

Part Number: **W17880-4PG-P-300**

UV resistant thermoplastic insert panel mount connector #22 crimp (supplied loose) 4-position pin (male) gold over nickel plating Insta-Click™ hex nut and gasket (no epoxy) no color option (standard black); No Wing (Standard)



Notes: PC Tail sizes .280 and .335 are only available in #20 contacts.
Insta-Click™ connectors are only available in black UV resistant material
Winged coupling nuts are only available on cable-end connectors
Consult factory for optional threaded coupling
Consult factory for custom designed cable assemblies and connectors.

