



STC-S133UVC-DALL

Board level camera, 1.3 MP, colour, 60 fps, 1280x960, 1/3.2" sensor, 3.5x3.5, ISX017, UVC, dual pass filter, case type, S
mount

Teknik Özellikler

Camera type	Color
Number of pixels	1.3 MP
Interface	UVC
Lens mount	S-mount
Shutter type	Rolling
Image width	1280 pixels
Image height	960 pixels
Image sensor format	1/3.2"
Image sensor type	ISX017
Pixel size	3.5 µm
Frame rate	60 fps
Optical filter	Dual pass filter
Lens type	Not Applicable
Scan type	Area scan

CAD Kütüphanesi



EAC Mark removal Üretimden Kaldırılma Bildirimi

EN PDF 221 KB



Industrial Cameras STC/FS Series Broşür

EN PDF 17,6 MB

SDK 1.0.4. MacOS Yazılım

EN PKG 78,9 MB

SDK 1.0.4. aarch64 Install

Yazılım

EN TXT 71,4 MB

SDK 1.0.4. armv7l Install

Yazılım

EN TXT 70,8 MB

SDK 1.0.4. x86_64 Install

Yazılım

EN TXT 74,6 MB

Sentech SDK Win32

Yazılım

EN DAT 140 MB

Sentech SDK x64

Yazılım

EN DAT 150 MB



StUVC Viewer

Yazılım

EN ZIP 612 KB