







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/07	
A		REDRAWN	11/18/13	KW/TW
B		REDRAWN	2/10/15	HR/NP
C		REVISED SPEC.	7/15/15	HR/YC



SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

Solder nail: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Current rating: 1 A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

-40°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 15

A = .049 [1.25] x No. of Spaces

B = .049 [1.25] x No. of Spaces + .118 [3.00]

C = .049 [1.25] x No. of Spaces + .071 [1.80]

D = .049 [1.25] x No. of Spaces + .230 [5.85]

PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES		ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE		TITLE	
DRAWN	BW	01/17/07		MX 1.25mm WAFER 90° SMT	
CHECKED				SIZE X	PART NO. 125SH-B-XX-TR-SMT-T/R
APPROVED				REV. C	
REF: S00124T		SCALE: NTS		SHEET 1 OF 1	