


CnC Tech

CABLE SPECIFICATION

Style	50618-4.0-1-0500-1-TS		
Spec.	H1Z2Z2-K 1×4.0mm ²		
	29AC11061BK002	Version	A0
Item		Unit	Specification
Awg		mm ²	4
No. of conductor		p,c	1C
Conductor	Material	---	Tinned Copper
	Construction	No./mm	56/0.285±0.008
	Stranded diameter)	mm	2.46(Ref.)
Insulation	Material	---	XLPE
	Nom. Thickness	mm	0.97(Ref.)
	Diameter	mm	4.40±0.15
	Color	---	White
Jacket	Material	---	XLPE
	Min. Thickness	mm	0.80
	Nom. Thickness	mm	0.85(Ref.)
	O.D	mm	6.10±0.15
	Color	---	Black
Marking	 TÜV H1Z2Z2-K 1×4.0mm ² -40°C to +90°C DC 1500V		
	Height : 1.5 FONT : F1		

Configuration:

- 1.Compliant with TUV EN50618.
- 2.Working Temp -40°C~+90°C.
- 3.Irradiation 8~12Mard
- 4.500FT/Reel



Sectional view

RATIFY	<i>Xuqiyou</i>	APPROVED	/	DESIGN	<i>Zhuraobing</i>
--------	----------------	----------	---	--------	-------------------

HJ-RNE-001-A0