C2G

Discontinued - 32.8ft (10m) LC-SC 50/125 OM2 Duplex Multimode Fiber Optic Cable (TAA Compliant) - Orange

Part No. 11051



Cost-effective solution that provides higher bandwidth and transmission rates and supports longer distances with lower loss than 62.5/125 fiber. Specifically designed for use with today's narrower aperture components, this cable is fully compatible with multimode applications. The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 50/125 multimode fiber, immune to electrical interference.

Features & Benefits

- Designed to support gigabit ethernet, fibre channel, ATM, and internet protocol applications
- Patented injection molding process for greater durability
- Optically inspected and tested for insertion loss
- Pull-proof jacket design, immune to electrical interference

Specifications

General Info

Product Line	C2G	Color	Orange
UPC Number	757120110514	Country Of Origin	Hong Kong
Application Sector	Commercial, Industrial	Type	Cable

Dimensions

Product Length US	32.8 FT	Cable Length	33 ft

Trade Programs

TAA Compliant	Yes

Technical Information

Fiber Optic Cable Type	Multimode, OM2	Jacket Material	PVC (Polyvinyl Chloride)
Bend Radius	45 mm	Simplex/Duplex	Duplex
Cable Type	Fiber Optic	Jacket Rating	Standard / Non-Rated
Data Transfer Rate	10 Gbps	Connector 2	SC Male
Connector 1	LC Male	Fiber Size	50/125

Downloaded from Arrow.com.