



**Part Number :** 936000046  
**Product Description :** Heavy-Duty Metal Cable Gland, with Washer and Gaskets, M20x1.5 Thread  
**Series Number :** 93600  
**Status :** Active  
**Product Category :** Heavy-Duty Cable Glands  
**Engineering Number :** 7000.6848.0



## Documents & Resources

### Product Environment Compliance

#### Compliance

|                    |                                                 |
|--------------------|-------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                    |
| China RoHS         | per SJ/T 11365-2006                             |
| EU ELV             | Not Relevant                                    |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                  |
| REACH SVHC         | Contains Lead per D(2025)4165-DC (25 June 2025) |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863   |

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

## Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

---

## Part Details

### General

|                  |                                                                       |
|------------------|-----------------------------------------------------------------------|
| Status           | Active                                                                |
| Category         | Cable Glands                                                          |
| Series           | 93600                                                                 |
| Description      | Heavy-Duty Metal Cable Gland, with Washer and Gaskets, M20x1.5 Thread |
| Cable Gland Type | IP66 - Basic                                                          |
| Comments         | 4 Gaskets: 4.00, 7.00, 10.00, and 13.00mm internal diameters.         |
| IP Rating        | IP66                                                                  |
| Product Name     | Heavy-Duty Connectors                                                 |
| UPC              | 887191826189                                                          |

### Physical

|                               |                              |
|-------------------------------|------------------------------|
| Cable Diameter                | 3.50-12.50mm                 |
| Material - Cable Gland        | Brass                        |
| Material - Gasket             | Elastomer                    |
| Material - Plating            | Nickel (body), Zinc (washer) |
| Material - Washer             | Steel                        |
| Net Weight                    | 21.000/g                     |
| Packaging Type                | Bag                          |
| Panel Mount                   | Yes                          |
| Temperature Range - Operating | -40° to +125°C               |
| Thread Size                   | M20x1.5                      |
| Thread Type                   | (M) Metric                   |

## Mates With / Use With

### Use with Part(s)

|             |             |
|-------------|-------------|
| Description | Part Number |
|-------------|-------------|

|          |                                    |
|----------|------------------------------------|
| Use With | Enclosures Size A and B metal type |
|----------|------------------------------------|

---

This document was generated on Sep 25, 2025