

# Product data sheet

Specifications



## APC Replacement battery cartridge #152 with 2 Year Warranty

APCRBC152

### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Product or component type	Replacement battery cartridge
Battery type	Lead-acid battery
Provided equipment	Installation guide

### Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cartridge
Number of battery replacement quantity	1

Replacement battery

### Physical

Colour	Black
Height	7.6 cm
Width	21 cm
Depth	76.2 cm
Net weight	15.29 kg

Mounting mode	Not rack-mountable
---------------	--------------------

## Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 % non-condensing
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 % non-condensing

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.3 cm
Package 1 Width	63.5 cm
Package 1 Length	34.3 cm
Package 1 Weight	17.55 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)