

1


2

3

4

5

RoHS Compliant



Notes:

1. Waterproof Rate: IP67
2. Electrical Characteristics:
Current Rating: 1A
Voltage Rating: 30V

PIN OUT:

P1

1 _____ Red(24AWG)
2 _____ White(28AWG)
3 _____ Green(28AWG)
4 _____ Black(24AWG)
Shell _____ Drain

P/N	L
107-1024-BL-00050	500±30
107-1024-BL-00100	1000±30
107-1024-BL-00150	1500±30
107-1024-BL-00200	2000±40

ITEM	DESCRIPTION	MATERIAL	PLATING & COLOR	Q'TY
1	USB Plug	USB 2.0 SMD	N/A	1
2	Screw Nut	PC	Black	1
3	Gasket	EPDM	Black	1
4	Cable	UL2725 24AWG*2C+28AWG*1P+ADB OD:4.7 UV Resistant	Black(PVC Jacket)	A/R
5	Outer molding	TPU	Black	A/R
6	Inner molding	TPU	Natrual	A/R
7	Heat Shrink Tube	OD:1.0 300V 125°	Black	1

DRAWN:

GENERAL TOLERANCE:

X=±5
.X=±0.5
.XX=±0.3

CHECKED:

UNIT: MM

SCALE: 1:1

APPROVAL:

SHEET: 1 / 1

PROJECTION:

CnC Tech

Industrial Cable and Connector Technology

DESCRIPTION: **WATERPROOF USB PLUG CABLE
ASSEMBLY**PART NO: **107-1024-BL-00XXX**

SIZE

A4

REV	DATE	FILE	BY
-----	------	------	----