

- Find by Feature
- Browse by Category
- Browse by Application
- Share

Search →

Enter part number or keyword

- Search Results (0)
- Search Options

No Search Results

Select a product type to narrow your search:

Mounting Device

Results with your selections: --

Component Type

-
- ☐ Bracket
- ☐ Clamp
- ☐ Clip
- ☐ Wire Tie



Search →

Clear

Component Feature

-
- ☐ Cable
- ☐ Conduit
- ☐ Connector
- ☐ Push Pin
- ☐ Snap On
- ☐ Strap
- ☐ Tape On



Search →

Clear

Fastening Type

-
- ☐ Attach base
- ☐ C-Clasp
- ☐ Edge
- ☐ Nail
- ☐ Oval Hole
- ☐ Push Nut
- ☐ Rosebud
- ☐ Round Hole
- ☐ Special



Search →

Clear

Hole diameter [mm]

-
- ☐ 3.60
- ☐ 5.60
- ☐ 6.00 - 7.00
- ☐ 6.10 - 6.60
- ☐ 6.10 - 7.00
- ☐ 6.25
- ☐ 6.30
- ☐ 6.30 - 7.00
- ☐ 6.30 - 8.00
- ☐ 6.35
- ☐ 6.40
- ☐ 6.40 - 7.00
- ☐ 6.50
- ☐ 6.50 - 7.00
- ☐ 6.50 x 13.00
- ☐ 6.60
- ☐ 6.63
- ☐ 6.65
- ☐ 6.70
- ☐ 7.00
- ☐ 7.00 - 7.50
- ☐ 7.00 x 10.00
- ☐ 7.00 x 12.00
- ☐ 7.10
- ☐ 7.10 - 7.30
- ☐ 7.50
- ☐ 8.00
- ☐ 8.00 x 15.00
- ☐ 8.00 x 15.50
- ☐ 8.30
- ☐ 8.50
- ☐ 8.50 x 16.00
- ☐ 8.60
- ☐ 8.80
- ☐ 9.00
- ☐ 10.00
- ☐ 10.60
- ☐ 11.00
- ☐ 12.00
- ☐ 13.00
- ☐ 16.00
- ☐ 20.00
- ☐ 25.00



Search →

Clear

Bundle size [mm]

-
- ☐ 1.00 - 35.00
- ☐ 4.00 - 28.00
- ☐ 4.00 - 45.00
- ☐ 5.00 - 28.00
- ☐ 5.00 - 30.00
- ☐ 6.00
- ☐ 6.00/10.00
- ☐ 6.00/9.00
- ☐ 7.00/13.00
- ☐ 7.90
- ☐ 7.92
- ☐ 8.00
- ☐ 8.00/10.00
- ☐ 8.00/13.00
- ☐ 8.50
- ☐ 9.00
- ☐ 9.00/13.00
- ☐ 9.00/25.00
- ☐ 9.00/30.00
- ☐ 10.00
- ☐ 10.00/13.00
- ☐ 10.00/16.00
- ☐ 12.00
- ☐ 13.00
- ☐ 13.00/16.00
- ☐ 15.00
- ☐ 16.00
- ☐ 18.00
- ☐ 19.00
- ☐ 20.00
- ☐ 22.00
- ☐ 25.00
- ☐ 28.00
- ☐ 30.00
- ☐ 35.00
- ☐ 40.00
- ☐ 40.80



Search →

Clear

Stud Size

-
- ☐ M10
- ☐ M12
- ☐ M5
- ☐ M6
- ☐ M8



Search →

Clear

Conduit Size [mm]

-
- ☐ 6
- ☐ 6/10
- ☐ 6/9
- ☐ 7/13
- ☐ 8
- ☐ 8/10
- ☐ 8/13
- ☐ 9
- ☐ 9/13
- ☐ 9/25
- ☐ 9/30
- ☐ 10
- ☐ 10/13
- ☐ 10/16
- ☐ 12
- ☐ 13
- ☐ 13/16
- ☐ 16
- ☐ 18
- ☐ 19
- ☐ 22
- ☐ 25
- ☐ 30
- ☐ 40
- ☐ 9/25



Search →

Clear

Color

-
- ☐ Black
- ☐ Blue
- ☐ Brown
- ☐ Cream
- ☐ Gray
- ☐ Gray Dark
- ☐ Gray Light
- ☐ Gray Medium
- ☐ Green
- ☐ Green Light
- ☐ Natural
- ☐ Orange
- ☐ White



Search →

Clear

Clear

Search →

Connector Attachment Clip

Rosebud, Attachment Hole Diam 6.35



Part #08905563

Question about this product?

- Attributes
- Documents (4)

Part #:	08905563
Description:	Connector Attachment Clip Rosebud, Attachment Hole Diam 6.35
Product Type:	Mounting Device
Fastening Type:	Rosebud
Status:	Active
Component Type:	Attachment Clip
Component Feature:	Connector
Hole size [mm]:	6.35
Nominal Metal Sheet Thickness [mm]:	3.8
Length [mm]:	0.25
Color:	Black
Material:	PP
Weight [g]:	0.49
ELV compliant:	Yes
RoHS compliant:	Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.