



OCEAN APPLICATORS



✓ Active

TE CONNECTIVITY (TE)
OC-AT-S-FM-090F145O-001-0216
[AMP](#)

2151204-1
TE Internal Number: 2151204-1

[Not in Scope for EU RoHS/ELV Compliance](#)

Region **Worldwide**

Tool Type **Applicator**

Spare Parts Tooling **No**

Applicator Style **OCEAN - Atlantic**

Applicator Feed Style **Side Feed**

Product Drawings

[Ocean Side Feed Applicator](#)

PDF
English

Catalog Pages/Data Sheets

[4-1773460-5_New Series Of Applicators From](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Tool Type	Applicator
Spare Parts Tooling	No
Applicator Style	OCEAN - Atlantic
Applicator Feed Style	Side Feed
Applicator Feed Type	Mechanical

Product Availability

Region	Worldwide
--------	------------------

Product Compliance

[Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)



Relation Type



RELATIONSHIP

Spare Parts

Spare Parts

See All Spare Parts



PRODUCT - SPARE PARTS

Application Tooling - OCEAN Applicators
AMP

FLOATING SHEAR
- 318707-1

TE INTERNAL NUMBER: 318707-1

✓ Active

Not in Scope for EU RoHS/ELV
Compliance

Region **Worldwide**

Tool Type **Applicator**

Spare Parts Tooling **Yes**

Spare Parts Tool Type **Shear**

RELATIONSHIP

Spare Parts

Spare Parts

See All Spare Parts



PRODUCT - SPARE PARTS

Application Tooling - OCEAN Applicators
AMP

ANVIL, COMBINATION
(.090) - 2-1333205-1

TE INTERNAL NUMBER: 2-1333205-1

✓ Active

Not in Scope for EU RoHS/ELV
Compliance

Region **Worldwide**

Tool Type **Applicator**

Spare Parts Tooling **Yes**

Spare Parts Tool Type **Anvil**

RELATIONSHIP

Spare Parts

Spare Parts

See All Spare Parts



PRODUCT - SPARE PARTS

Application Tooling - OCEAN Applicators
AMP

CRIMPER, WIRE .090
- 2-456406-9

TE INTERNAL NUMBER: 2-456406-9

✓ Active

Not in Scope for EU RoHS/ELV
Compliance

Region **Worldwide**

Tool Type **Applicator**

Spare Parts Tooling **Yes**

Spare Parts Tool Type **Crimper**