



Powering Business Worldwide

pe.eaton.com

Eaton Bussmann series EuroMag EM2565 terminal block

EM256506HL1

UPC:051712902694

Dimensions:

- **Height:** .571 IN
- **Length:** 1.2 IN
- **Width:** .72 IN

Weight: .05 LB

Warranties:

- Eaton Selling Policy 25-000 generally applies with some exceptions. Drive products come with a standard 24 months from date of shipment and 36 months with Eaton certified start up all inclusive coverage parts labor and travel.

Specifications:

- **Application:** industrial
- **Type:** Pluggable, horizontal
- **Voltage Rating:** 300 V
- **Number Of Poles:** Six-pole
- **Operating Temperature:** -40° to 105°C
- **Wire Size:** #26-12 AWG Cu
- **Screw Size:** M3.0 zinc plated steel
- **Wire Range:** #12-24 AWG
- **Torque Rating:** 7 lb-in
- **Center Spacing:** 0.200 in
- **Contact Material:** Tin plated brass
- **Housing Material:** UL rated 94V0 thermoplastic
- **Orientation:** Horizontal
- **Material:** Thermoplastic housing, tin plated brass contacts, zinc plated steel screw
- **Connection:** M3 X 5 screw



Supporting documents:

- [Product Catalog](#)

Certifications:

- UL Recognized

Product compliance:

- CE Marked
- RoHS Compliant
- EU Directive 2002/95/EC Category 3 (4 of 5)

© 2016 Eaton. All rights reserved.