

RECTANGULAR CONNECTOR HOODS



✓ Active

TE CONNECTIVITY (TE)

H10B-SGRH-2M32

HDC | HDC Hood & Housings , HDC IP 65 Hood & Housing

T1470102232-000

TE Internal Number: T1470102232-000

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

Accessory Type Hood

Entry Style Side

Locking Device Location Housing

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

H10B-SGRHS-PG/M

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

[HDC Flyers July 2015 \(Chinese\)](#)

PDF

[HDC Connectors - July 2015 \(English\)](#)

PDF

English

Product Specifications

Product Specification

[HB Series IP65 Housing & Hood](#)

PDF

English

[HB Series IP65 Housing & Hood](#)

PDF

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Accessory Type Hood

Thread Size PG2x16

HTS Housings and Hoods Yes

Body Features

Entry Style Side

Material Die Cast Aluminum

Mechanical Attachment

Locking Device Location Housing

Dimensions

Length (mm) 94

Height (mm) 74

Width (mm) 57

Usage Conditions

Corrosion Protected Yes

Packaging Features

Packaging Method Box

Statement of Compliance

Statement of Compliance

PDF
