



**Part Number :** [734154491](#)  
**Product Description :** MCX Plug, Straight, Crimp, RG-179 Cable, Die Cast Body, Gold (Au) Plated, One Piece Per Bag, 75 Ohms  
**Series Number :** 73415  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors



Documents & Resources


**Drawings**  
[734154491\\_sd.pdf](#)

**3D Models and Design Files**  
[734154491\\_stp.zip](#)

**Specifications**  
[735970700-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	RF / Coaxial Connectors
Series	73415
Description	MCX Plug, Straight, Crimp, RG-179 Cable, Die Cast Body, Gold (Au) Plated, One Piece Per Bag, 75 Ohms
Product Name	MCX
Style	Cable
Type	Microminiature
UPC	884982691544

#### Electrical

Frequency	6 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

#### Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	2.400/g
Orientation	Straight
Packaging Type	Individual Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-179

---

---

This document was generated on Apr 26, 2025