

- Circuit Board Indicators
- Panel Mount Indicators
- Solid State Lighting
- Traffic Signals
- Vehicle Lighting
- Rail
- Obstruction Lighting
- Hazardous Area Lighting
- Heliport Lighting

- how to purchase
 -  sales contacts
 -  stock check

 search

 Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

☐ Part # / Text Search

Part No.:

Text Search:

 quick links


Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators	
P/N# 5530121410F	3 mm Lens
Description	3 mm Bi-Level CBI
Package Options	50 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Bi-Level Housing
Configuration	3 mm Lens
Viewing	Right Angle
Viewing Angle	60
Test Current (mA)	10mA
Absolute Maximum Ratings (T _a = 25 °)	
Solder Temp	260Â° for 5 sec
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C



Operating Characteristics			
LED Position	Found in position(s): 1	Found in position(s): 2	
Color	Red	Green	
Lamp Type	Single Color	Single Color	
LED Type	High Efficiency	High Efficiency	
Intensity Min (mcd)	7.4	4.7	
Intensity Typ (mcd)	10.0	12.6	
Intensity Max (mcd)			
Fwd Voltage Min			
Fwd Voltage Typ			
Fwd Voltage Max			
Dom Wavelength Min (nm)			
Dom Wavelength Typ (nm)			
Dom Wavelength Max (nm)			
Power Dissipation Max (mW)	100	100	
Backlighting			
Pitch Between Vertical			
Pitch Between Horizontal			
Lum Intensity Min			
Lum Intensity Typ			
Lum Intensity Max			

Distributor Stock Check

Check stock with our distributors now.

5530121410F

[check stock](#)