





Mating Cycles	500
Filter type	C
Capacitance	3900pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB

							Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, female, straight, 15 Poles, turned solder pins, tin plated shell with spacer nuts and board-locks	Mo?Mstob/ Scale 1.5:1
						Detail.	8-JUL-02	CV			
						Insp.					
						Stand.					
09642127246	M3		33250	03/11/05	JMDR	HARTING EURL F-95972 Paris				TB 0964212724x	Blatt/ Page 2 / 3
09642127245	UNC 4-40		31058	8-JUL-02	CV						
Part number	Nut thread		Mod.	Dat.	Name						