










PCB layout, component side




Max. Temperature: 260° during 10 seconds.

0955 469 3821 741	1	M3	Black insulator	Reel Packaging: 140 connectors (See details on page2/2)
0955 469 3822 741	1	4-40 UNC		
0955 469 6821 741	2	M3		
0955 469 6822 741	2	4-40 UNC		
0955 469 7821 741	3	M3		
0955 469 7822 741	3	4-40 UNC		
Part number	PL	Screw lock	Index designation	

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances		
				Dat.	Name	Scale 1.5:1	D-Sub SMT, 37 poles Male, Straight with screw locks and ground pins	
			Detail.	25-Oct-11	Johnson.S			
			Insp.	17-Nov-11	Steven.W			
			Stand.	17-Nov-11	Steven.W			
			Zhuhai HARTING Limited			TB 09 55 469 x82x		Page 1 / 2
EC04070	17-Nov-11	Johnson.S				Sub.		
Mod.	Dat.	Name						



Detail A



See TB 09 55 469 x82x folio 1/2
for connector dimensions
and PCB layout

Packaging in accordance with
EIA 481-2.

0955 469 3821 741	1	M3	Black insulator	Reel Packaging: 140 connectors
0955 469 3822 741	1	4-40 UNC		
0955 469 6821 741	2	M3		
0955 469 6822 741	2	4-40 UNC		
0955 469 7821 741	3	M3		
0955 469 7822 741	3	4-40 UNC		
Part number	PL	Screw lock	Index designation	

			All Dimensions in mm Original Size DIN A 3				Techn. Character.			Free size tolerances		
					Dat.	Name	Scale	D-Sub SMT, 37 poles Male, Straight with screw locks and ground pins				
			Detail.	25-Oct-11	Johnson.S							
			Insp.	17-Nov-11	Steven.W							
			Stand.	17-Nov-11	Steven.W							
			Zhuhai HARTING Limited						TB 09 55 469 x82x			Page
EC04070	17-Nov-11	Johnson.S							Sub.			2/2
Mod.	Dat.	Name										