

Part Number : [197054201](#)

Product Description : PCB Tab Quick Disconnect, Male, for Wire, Box, Tab 6.35 x 0.81 mm, Carton

Series Number : 19705

Status : Active

Product Category : Quick Disconnects



Documents and Resources

Drawings

[197054201_sd.pdf](#)

[PK-19511-600-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)


Specifications

[PS-19902-010-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19705
Description	PCB Tab Quick Disconnect, Male, for Wire, Box, Tab 6.35 x 0.81mm, Carton
Comments	Tab Support
Product Name	PCB Tab
Type	PCB Tab
UPC	800754883498

Agency

UL	E79133
----	--------

Electrical

Voltage - Maximum	N/A
-------------------	-----

Physical

Barrel Type	N/A
Gender	Male
Glow-Wire Capable	No
Insulated	No

Insulation	None
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.500/g
Orientation	PCB Straight Tab
Packaging Type	Carton
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

This document was generated on May 20, 2026