






FRONT OPENNING



BACK OPENNING



REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD
1		ADD PART NO.	Garvey 9/16/00	
2		DIMENSION MODIFY	zling 07/08/01	
3		DRAWING MODIFY	LWL 11/26/02	
4		ADD PART NO.	CHI 05/05/03	
5		DRAWING MODIFY	COKE 10/27/03	
6		ADD PART NO.	CECILIA 3/03/04	

IDC Connect Modular Jack

These jacks are available in two versions to meet either shielded or unshielded application requirements on twisted pair cable. They are also available in the two most commonly used wiring schemes. They are perfectly design to use with wallplates, faceplates and patch panels.

NOTE:

1. PART NUMBER: E6188-X1X025

- 1- T568A
2- T568B
- 1- AWG # 22
2- AWG # 24
3- AWG # 26With Strand Wire
4- AWG # 30

- E6188-X1X025-L WITH NO LEAD
- 1- T568A
2- T568B
- 1- AWG # 22
2- AWG # 24
3- AWG # 26With Strand Wire
4- AWG # 30

MM (INCH)		DFTO JAME	DATE 01/06/98	FULL RISE ELECTRONIC CO., LTD	
TOLERANCES EXCEPT AS NOTED		CHKD ZY	DATE 2004/3/3		
DETACHED LISTS	MM			TITLE FULLY SHIELDED CAT.5 KEYSTONE JACK	
	.0 ±0.20				
	.00 ±0.15			DRAWING NO. GE613001	
	.000 ±0.075				
ANGLES ±		APPVL SHY	DATE 2004/3/3	/PART NO. SEE NOTE	
THIRD ANGLE PROJECTION		MATERIAL :			
		QT'Y :		DO NOT SCALE DRAWING	
		FINISH :			
		SCALE : 2:1		SHEET X OF Y	