
CLIFF

METAL 3 PIN XLR SOCKETS


(FEEDTHROUGH STYLE)





FC61900 - FEMALE XLR 3DCF/BM BLACK WITH LATCH
FC61900N - FEMALE XLR 3DCF/NM NICKEL WITH LATCH






FC61905 - MALE XLR 3DCM/BM BLACK
FC61905N - MALE XLR 3DCM/NM NICKEL

SPECIFICATION

Contact Resistance: ≤7mΩ
Insulation Resistance: ≥5000MΩ
Withstand Voltage: 1400V
Durability (Mating / Unmating): ≥2000 insertions
Insertion and Extraction force: 10-80N



These metal 3 pin XLR's can be fitted into our 1U racks.



© CLIFF 11/18 ISS.2

For further information, contact sales@cliffuk.co.uk

Cliff Electronic Components Limited,
76 Holmethorpe Avenue, Holmethorpe Ind. Estate,
Redhill, Surrey RH1 2PF U.K.
Tel: +44 (0)1737 771375 Fax: +44 (0)1737 766012

www.cliffuk.co.uk

✓RoHS

Downloaded from Arrow.com.