

Detailed Specifications

Frame Width:	35[mm]
Frame Height:	35[mm]
Frame Depth:	15[mm]
Max. Air Flow:	5.7[CFM]
Max. Air Flow:	0.16[m3 per min]
Max. Static Pressure:	0.14[In H2O]
Max. Static Pressure:	35[Pa]
Fan Speed:	8000[RPM]
Noise:	24[dB]
Life Expectancy:	40 degree C 30,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.2[V]
Current:	0.07[A]
Input Power:	0.8[W]
Mass:	12.5[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active