This document was generated on 05/31/2019


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1722562105

Status: Active

Overview: Ultra-Fit Power Connectors

Description: Ultra-Fit TPA Receptacle Housing, 3.50mm Pitch, Single Row, 5 Circuits, Natural, Glow-Wire Capable



Series image - Reference only

Documents:

3D Model
Drawing (PDF)
Product Specification 1723230001-TS-000 (PDF)
Product Specification PS-172323-0001-001 (PDF)
Application Specification AS-172323-0001 (PDF)
RoHS Certificate of Compliance (PDF)
Product Literature (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	172256
3D Viewer	Yes
Application	Power, Wire-to-Board
Overview	Ultra-Fit Power Connectors
Product Literature Order No	987651-1008
Product Name	Ultra-Fit
UPC	887191734088

Physical

Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.710/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +120°C

Solder Process Data

Lead-freeProcess Capability	N/A

Material Info

Reference - Drawing Numbers

Application Specification	AS-172323-0001
Product Specification	1723230001-TS-000, PS-172323-0001-001
Sales Drawing	SD-172256-0001-000

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant

REACH SVHC
Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
172256 Series

Mates With
Ultra-Fit Right Angle Header 172310
Ultra-Fit Vertical Header 172286 , 172287

Use With
Ultra-Fit Female Crimp Terminal 172253
Ultra-Fit TPA Retainer 172264

This document was generated on 05/31/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.