

Product data sheet

Specifications



APC IT Power Distribution Module 3 Pole 5 Wire 20A 240V IEC309 440cm

PDM3520IEC309-440

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

General

Provided equipment	Installation guide
--------------------	--------------------

Physical

Colour	Grey
Depth	40.6 cm
Height	12.7 cm
Net weight	4.45 kg
Width	44.4 cm

Input

Network frequency	60 Hz
Plug standard	IEC 60309
Permissible voltage	200...240 V
Max line current	20 A
Input voltage	230 V

Output

Max current draw	20 A
Number of power socket outlets	1 IEC 309
Output voltage	240 V

Conformance

Product certifications	UL listed
------------------------	-----------

Packing Units

Package 1 Weight	5 kg
------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	12.7 cm
Package 1 width	44.4 cm
Package 1 Length	40.6 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------