





Rev	AWO #	Description	Date	Appr
-		RELEASED	1/21/10	

APPROVED: _____
DATE: _____ TITLE: _____



SEC. A-A



SEC. B-B

P/N	Wire size	Dim. a	Dim. b	Dim. c	Dim. d
DMT-A-C-M-T-R	#26~#30AWG	.071 [1.80]	.063 [1.60]	.094 [2.40]	.075 [1.90]
DMT-B-C-M-T-R	#20~#24AWG	.083 [2.10]	.083 [2.10]	.106 [2.70]	.094 [2.40]

SPECIFICATIONS:

Material: Phosphor Bronze, 0.2mm thick
Plating: Tin over copper underplate overall.

Electrical:
Operating voltage: 250 VAC RMS max
Current rating: 20 Awg: 5 Amps max
22 Awg: 5 Amps max
24 Awg: 4 Amps max
26 Awg: 3 Amps max
28 Awg: 2 Amps max
30 Awg: 1 Amp max

Mechanical:
Wire size: 20 Awg thru 30 Awg
Environmental:
Lead free, RoHS compliant.

Dielectric resistance: 10 mohms max.
Temperature rise: 30° max.

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .118" [3.0mm] CRIMP TERMINAL,
TIN PLATED, ON REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED				HOLDERS			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	DR	1/21/10					
CHECKED							
APPROVED							
SIZE	PART NO.	REF:	SCALE:	NTS	SHEET	1 OF 1	REV.
X	DMT-X-C-M-T-R	REF: S00004T	SCALE: NTS				-

A

B

C

D

A

B

C

D