HellermannTyton

Technical data sheet

Article number:
561-01611 WIC1-1



Product Group	Pre-printed cable markers
Product Family	WIC, snap on
Material	Polyamide 6.6 (PA66)
Colour	Brown (BN)

Application Tool	WIC Tool
Bundle Ø max.	2.80 mm
Bundle Ø min.	2.00 mm
Flammability	UL 94 V0
Height (H)	6.40 mm
Length (L)	3.0 mm
Marking Text	1
Operating Temperature	-40 °C to +85 °C
Package Content	1000 pcs.
Package Content packed in	box
Print Method	inkjet print
Specifications	EN 60062, IEC 304
Width (W)	5.00 mm
Wire Size Range (mm²)	0.50-1.50 mm²

HF RoHS

created on 31. July 2026, 2:10 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.