


Technical data sheet

Article number:
308-32400

HIS-3-24/8



Product Group	Heat shrinkable tubing 3:1 on a reel
Product Family	HIS-3
Material	Polyolefin, cross-linked (PO-X)
Colour	Black (BK)
Behaviour at Heat Shock	not fluid, not dripping, not cracking
Behaviour at Low Temperature [Test method]	not cracking [UL 224]
Dielectric Strength [Test method]	32 kV/mm [IEC 60243]
Elongation at break [Test method]	800 [ASTM D2671]
Elongation At Heat Aging	400 %
Flammability	UL 224 VW-1
Heat Aging Test [Test method]	168h/175°C [UL 224]
Heat Shock Test	4h/250°C
Insulation Class	B (VDE 0530)
Longitudinal Change After Shrinkage	+/-5%
Min. Shrink Temperature - °C	+100 °C
Minimum Tensile Strength At Heat Aging	13 MPa
Operating Temperature	-55 °C to +135 °C
Package Content packed in	pcs.
Pack Cont.	3 m
Recov. Ø d max.	8.0 mm
Shrink Ratio	3:1
Specifications	ANSI/UL 224, C22.2 no. 198.1-06
Supplied Ø D min.	25.4 mm
Tensile Strength [Test method]	14 MPa [ASTM D2671]
UL-File Number	E143529
Wall (WT)	1.00 mm

