
**Part Number :** 528520770
**Product Description :** Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Right-Angle, Non-ZIF, Bottom Contact Style, 7 Circuits
**Series Number :** 52852
**Status :** Active
**Product Category :** FFC / FPC Connectors



## Documents and Resources

### Drawings

528520770_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

528529200-200.pdf

PS-52852-014-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | FFC / FPC Connectors |
| Series | 52852 |
| Description | Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Right-Angle, Non-ZIF, Bottom Contact Style, 7 Circuits |
| Contact Type | Bottom |
| Product Name | Easy-On |
| UPC | 822348122967 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 50V |

### Physical

| | |
|---|---|
| Actuator Type | Non-ZIF |
| Circuits (Loaded) | 7 |
| Contact Position | Bottom |
| Durability (mating cycles max) | 10 |

Downloaded from Arrow.com.

| | |
|---|---|
| Mated Height | 3.10mm |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin-Bismuth |
| Material - Plating Termination | Tin-Bismuth |
| Net Weight | 251.300/mg |
| Orientation | Right Angle |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Mounting | Surface Mount |
| PCB Retention | No |
| Pitch - Mating Interface | 1.00mm |
| Pitch - Termination Interface | 1.00mm |
| Plating min - Mating | 1.016µm |
| Plating min - Termination | 1.016µm |
| Polarized to PCB | No |
| Stackable | No |
| Temperature Range - Operating | -20° to +80°C |
| Wire/Cable Type | FFC/FPC |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| 1.00mm Pitch Premo-Flex FFC Jumpers | 15167 |
| 1.00mm Pitch Premo-Flex FFC Jumpers | 15267 |
| 1.00mm Pitch Premo-Flex FFC Jumpers | 98267 |



Downloaded from Arrow.com.