



**CT40400SSBC0, Nylon Cable Tie,  
40 lb Tensile Strength, Stainless  
Steel Barb, 14.49" Long, Black**

By Burndy  
Catalog # [CT40400SSBC0](#)

Nylon Stainless Steel BARB Cable Ties, 14.49 IN L, .14 IN W,  
Tensile Strength: 40 Lbs,Color:Black.

**Features**

- Stainless Steel Barb Tie
- Nylon 6/6, Self-locking
- Maximum strength and adjustability for versatility

**Application**

For use with self-locking stainless steel barb

**General**

Catalog Number	CT40400SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	40 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT-SSB
UPC	781810564578
UPC 14 Digit GTIN	00781810564578

**Dimensions**

Dimension - Bundle Diameter Max inch	4.09
Dimension - Width inch	0.14 in
Dimension - Width mm	3 mm

**Certifications And Compliance**

Standards - RoHS Compliance Status	CM
------------------------------------	----

**Logistics**

Carton Quantity	8000
Minimum Pack Quantity	100

**Product Assets**

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT40400SSBC0](#)

