

Han M Protect Cover Die Cast for Hood PG



Image is for illustration purposes only. Please refer to product description.

Part number	09 37 003 5402
Specification	Han M Protect Cover Die Cast for Hood PG
HARTING eCatalogue	https://b2b.harting.com/09370035402

Identification

Category	Accessories
Series of hoods/housings	Han [®] M
Type of accessory	Protection cover
Description of the accessory	for hoods Metal With fixing cord

Version

Size	3 A
Locking type	Single locking lever
Details	for mounted male insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	30.38 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140055278
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors