





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/2/21	
A		UPDATE DIM.	10/28/21	LH/LL1
B		ADDED DIM.	11/25/24	LH/KC



SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating:
Gold flash over Nickel underplate overall
Electrical:
Current rating: 1 Amp.
Contact resistance: 20 mohms max.
Insulation resistance: 1,000 Mohms min.
Dielectric withstanding voltage: 500 VAC/DC
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant



△ Positions: 10 thru 40
A = .100 [2.54] x No. of Positions per Row + 1.184 [30.08]
B = .100 [2.54] x No. of Positions per Row + .894 [22.70]
C = .100 [2.54] x No. of Positions per Row + .369 [9.38]
D = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN	JJ	9/2/21
CHECKED	KL	9/2/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE .100 [2.54] IDC CARD EDGE SOCKET W/ROUND HOLE MOUNTING EAR		REV. B	
SIZE X	PART NO. FCE-XX-G-MH	REF: S00019C	SHEET 1 OF 1