

MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91829

SWITCH-ENCLOSED

CATALOG LISTING
BZE6-2RQ5

BZE6-2RQ5

M

DRAWING
NUMBER

9

8

ISSUE

3

REPLACES

RELEASE NO.

29AUG07

PSR

CHECK

77

ROB

CHECK

77

SEP

2



KPK

CHECK

77

SEP

2



NOTES-

- 1 - 6-32 UNC X .219 REF BINDING HEAD TERMINAL SCREW AND CUPWASHER (3)
- ² FURNISHED UNASSEMBLED
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F
- 4 - SEAL RATING: NEMA1
IP40

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 9-13 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 4 OZ MIN	15A-125, <u>250</u> OR 480 VAC, 2A-600 VAC 1/8 HP-125 VAC; 1/4 HP- <u>250</u> VAC 1/2A-125 VDC; 1/4A-250 VDC CODE L74	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL ----- .002 MAX	CE 1.5A, 240 Vac	TOLERANCES ARE:
OVERTRAVEL ----- .219 MIN		ONE PLACE (.0) ±.030
BASIC SWITCH REPLACEMENT -- BZ-2RQ724		TWO PLACE (.00) ±.015
		THREE PLACE (.000) ±.005
		ANGLES ±.005
		WEIGHT .53 LB

RASTER
FO-5285 1-A

DRAWN