

Amphenol® RF

PRODUCTS

▼

AMPHENOL RF PART NUMBER

901-173

SMA Straight Clamp Jack for RG-188 Double Braided, Bulkhead, 50 Ohm



FIND STOCK & BUY NOW

ADD TO COMPARE

ADD TO PART LIST

PRODUCT OVERVIEW

▼

SMA Straight Clamp Jack for RG-188 Double Braided, Bulkhead, 50 Ohm

Product Type	Connectors
Product Series	SMA
Status	Active

DOWNLOADS

▼

 901-173 3D Model File (Size: 291.1 KB) *

* Please [Login](#) or [Register](#) to download file

PRODUCT SPECIFICATIONS

▼

Gender	Jack
Orientation	Straight
Termination Style	Cable - Clamp
Impedence (Ohms)	50
Body Finish	Gold
Body Material	Beryllium Copper
Contact Finish	Gold
Contact Material	Beryllium Copper
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	B2
Cable Type	M17/152-RD316, RG-179 DB, RG-188 DB, RG-316 DB
Coupling Mechanism	Threaded
Mounting Feature	Bulkhead - Rear Mount
Max Frequency (GHz)	12.4
Polarity	Standard

Thread Direction	Standard
Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	100

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C - View Certificate
-------------	--

Additional compliance information is available in our [Product Compliance Center](#).

FOLLOW US

NEWSLETTER

AMPHENOL RF

QUICK LINKS

CONTACT US

Copyright © 2014 Amphenol RF. All Rights Reserved.
Copyright | Terms & Conditions | Privacy Policy | Logos | Amphenol.com