Specifications



Photo is representative





Eaton HC3-2R2-R

Eaton HC3 inductor, 2.05 uH, 78 A Irms, 60 A ISAT, 0.42 mΩ resistance, SMT mounting, Ferrite, 2-pins, 24 qty.

General specifications	
PRODUCT NAME	Eaton HC3 inductor
CATALOG NUMBER	HC3-2R2-R
UPC	051712897464
EAN	5027590148368
PRODUCT LENGTH/DEPTH	1.18 in
PRODUCT HEIGHT	0.689 in
PRODUCT WIDTH	0.996 in
PRODUCT WEIGHT	0.086 lb
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	78 A
ISAT	60 A
PACKAGE QUANTITY	24
MATERIAL	Ferrite
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.42 mΩ
SERIES	HC3

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - HC3-2R2-R Eaton HC3 high current power inductors data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2026 Eaton. All Rights Reserved.

Downloaded from Arrow.com.