**Part Number :** 1301420039
**Product Description :** Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L17-30, 3ø 600V
**Series Number :** 130142
**Status :** Active
**Product Category :** Wiring Devices
**Engineering Part Number :** 2877



## Documents and Resources

### Drawings

1301420039_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Wiring Devices |
| Series | 130142 |
| Description | Super-Safeway Plug with Locking Blade, 3 Pole/4 Wire, NEMA L17-30, 3ø 600V |
| IP Rating | N/A |
| NEMA Configuration | NEMA L17-30 |
| Product Name | Super-Safeway |
| Specialty | N/A |
| Type | Plug |
| UPC | 78678870628 |

### Agency

| | |
|---|---|
| CSA | LR6837 |
| UL | E10176 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 30.0A |
| GFCI | No |
| Voltage - Maximum | 3Ø 600V |

### Physical

| | |
|---|---|
| Cord Type | N/A |
| Flange | No |
| Flip Lid | No |
| Gender | Male |
| Length | N/A |
| Lighted Connector | No |

Downloaded from Arrow.com.

| | |
|---|---|
| Locking Blade | Yes |
| Net Weight | 1.000/g |
| Poles | 3-pole/4-wire |
| Receptacle Type | N/A |



Downloaded from Arrow.com.