



Part Number: 46999-0510

Image not available

Series image - Reference only

Status: Active - Custom

Series: [6410](#)

Category: Molex Parts

Old Part Number: AE-6410-04A(102)

Product Environmental Compliance

EU ELV:Not Relevant

EU RoHS:Compliant

China RoHS: 

REACH SVHC:Contains SVHC(June 15, 2015): No

Low-Halogen Status:Low-Halogen

Part Detail

General

Status Active - Custom

Category Molex Parts

Series [6410](#)

UPC 887191232461

Physical

Net Weight 0.464/g

Solder Process Data

Duration at Max. Process Temperature (seconds) 005

Lead-free Process Capability WAVE

Max. Cycles at Max. Process Temperature 001

Process Temperature max. C 235

Material Info

Old Part Number AE-6410-04A(102)

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)