
HellermannTyton

Technical data sheet

Article number:
169-60013 **CTN340**



Product Group	Convoluted Tubing
Material	Polyamide 6 (PA6)
Colour	Black with Grey Stripe (BKSTGY)

Diameter (D)	25.12 mm
Flammability	UL 94 HB
Halogen-free	No
Inside Ø (ID)	19.28 mm
Length (L)	152.4 m
Nominal Ø	19.05 mm
Operating Temperature	-40 °C to +125 °C
Outside Ø (OD)	25.12 mm
Package Content	167.60 m
Package Content packed in	carton

RoHS

created on 15. May 2026, 6:09 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.