



Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.




Kontaktkammer geschlossen
Contact chamber closed







Polzahl / No. of contacts	3 + PE
Anschlußart / Termination	crimpen / crimp
Anschlußquerschnitt / Wire gauge	0,14 - 1,5 mm² / AWG 26 - 16
Bemessungsspannung / Rated insulation voltage	600 V
Strombelastbarkeit / Current carrying capacity	13 A / +55°C 13 A / +131°F
Betriebstemperatur / Operating temperature	-40°C ... +125°C -40°F ... +257°F
Schutzart / Protection Class	IP 65 / IP 67
Anschließbare Kabeldurchmesser/ Using cable diameter	6 - 12,5 mm
Verriegelung / Locking system	Rundgewinde / round thread



Kontaktkammern Nr. 2, 4 und 6 geschlossen.
Contact chambers No. 2, 4 and 6 are closed.

Kontakte bitte separat bestellen.
Please order contacts separately.

Masse (errechnet)/*Calc WT:* 9		Zul. Abw./*Tolerances:*	Maßstab/*Scale* 2:1 (1:1) A3
Prüfmaß/*Testdimension*		DIN/ISO 13715	CUSTOMER DRAWING
Teileindex *Partindexnumber*		08 Datum/*Date* Name	Kabeldose 3+PE
		Gez. / *Drawn* 05.02. Cionvica	Female cable connector 3+PE
		Gepr. / *Checked* ?	
01 200800091 05.02.08 CI		Amphenol-Tuchel Electronics GmbH	M C016 10D003 806 12
Index Änderung/*Description* Datum/*Date* Name			Blatt/*Sheet* 1 1 Bl.
			Ers. f./*Replacement for:*

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

Downloaded from Arrow.com.