





**TOP VIEW**



**SECTION B-B  
END VIEW**



**SECTION A-A  
SIDE VIEW**



STEEL PANEL  
ORDER SEPARATELY


POLYCARBONATE  
VERSION ONLY  
UL US LISTED  
FILE #E65324  
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)  
Contact Factory (modshop@hammfg.com) for quotes  
Solid models of this enclosure available in .stp or .x\_t  
(Part number and text placement/orientation on our products are subject to change,  
we do not recommend using them as a locating reference for modification purposes)


**NOTE**

4 cover screws, and  
preformed silicone gasket.  
General Purpose ABS version is not UL approved. (Matl UL94 - HB)  
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

**Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)**



**INSIDE BOX**



**INSIDE LID**

1555B	
1555B Regular Enclosure	
General Purpose ABS RAL-7035	1555BGY
Polycarbonate RAL-7035	1555B2GY
ACCESSORIES	
Steel Inner Panels	1554BPL
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100)	1598ATS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50
Silicone Pre-formed Gasket Black (Pkg 2)	1554BGASKET

Dimensions:  
mm  
[inches]

**HAMMOND  
MANUFACTURING**  
**1555B**  
www.hammondmfg.com