



REV.	DATE	DESCRIPTION
NC	04/01/98	INITIAL RELEASE

DIMENSION NOTES:

L1 = 3.2mm MAX.
L = 26.7mm



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS		DATE	 Connector Corporation					
1 BODY	BRASS	NICKEL	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DRAWN	G.R.S.	04/01/98	TITLE BULKHEAD RECEPTACLE JACK (75 ohm)					
2 INSULATOR	DELIRIN	NATURAL			CHECKED								
3 CONTACT PIN	PHOS. BRONZE	GOLD			ISSUED								
4 FERRULE	COPPER	NICKEL											
5 HEX NUT	BRASS	NICKEL							SIZE	FSCM NO.	DWG. NO.	122333.DWG	REV.
6									A	99001			NC
7													
8					DO NOT SCALE DRAWING				SCALE	NA	PART NO.	122333	SHEET 1 OF 1