Part Number : 1301470080
Product Description : Watertite Extreme Extra Hard Outdoor Plug with Locking Blade, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V, Cord Grip Body Size F4, Black
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 28W75BLK



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Extra Hard Outdoor Plug with Locking Blade, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V, Cord Grip Body Size F4, Black
IP Rating	IP69K
NEMA Configuration	NEMA L15-30
Product Name	Watertite Extreme
Specialty	N/A
Type	Plug
UPC	78678875367

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	3Ø 250V

Physical

Cord Grip Body Size	F4 1"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	3-pole/4-wire

Downloaded from Arrow.com.

Receptacle Type	N/A

This document was generated on Sep 03, 2026

Downloaded from Arrow.com.