



0 Reviews



0 Reviews

Need Help?

SHOP PRODUCTS

All Search by keyword, connector, or sku



LIVE CHAT & HELP

Browse All Products | Cat5e / Cat6 / Cat6a | Cat5e | Cat5e Keystone Jacks

Loading...

# Cat5E RJ45 UTP Keystone Jack - White

180° 110/KRONE IDC punchdown; T568A/B



0 Reviews

Product #: 03791

Connector 1: (1) RJ-45 Female

Colors:

White
  Blue
  Grey

+ show all colors

Roll over image to zoom in

484 In Stock & ready to ship!



Add



### Need it shipped today?

Place your order before the timer runs out!

09: 19: 32

print share chat

Product Info

Customer Reviews

Questions & Answers

Distributors

More Choices

Description

Features

Certifications

Specs

Uses

Contents

## Product Description

Designed for superior performance, this keystone jack will work with C2G, formerly Cables To Go, wall plates or any standard keystone and angled multimedia wall plate or patch panel. Available in 9 colors to match housing or allow color-coded port designation in compliance with TIA-606 requirements. Each keystone jack includes 110-type IDC straight-back termination with strain relief caps, and comes standard with 50 µinch gold plating on the jack contacts.

**Please Note:** Not compatible with C2G surface mount boxes.

**WARNING:** Cancer and Reproductive Harm [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Product Certifications



## Product Specifications

Color: White

757120037910

<b>Warranty :</b>	Lifetime
<b>Vendor :</b>	C2G
<b>Weight :</b>	0.030 LB

**For more detailed specifications, please [read this](#).**

- Panel-type unshielded RJ45 (8P8C) keystone jack
- Meets or exceeds industry standard TIA/EIA 568-A-5 requirements
- Balances signal transmission of insertion loss and crosstalk from 1 to 100 MHz
- 110/KRONE IDC vertical punchdown termination for 22-26 AWG UTP solid wire
- Compatible with T568A and T568B wiring with Category 5 enhanced requirement
- Complies with FCC Part 68

#### Electrical Characteristics

- Current Rating - 1.5A
- Dielectric Withstanding Voltage - 1000VAC @60Hz
- Insulation Resistance - 500 M $\Omega$  (minimum)
- Contact Resistance - 20M $\Omega$  (maximum)
  
- Approvals - RoHS Compliant
- Warranty - Lifetime
- Package Type - Polybag

#### 2 Twisted Pairs

- DC Resistance - 0.139  $\Omega$ /m @20°C
- Dielectric Strength - 750VAC/minute min
- Insulation Resistance - 100 M $\Omega$ /KM @20°C

#### Mechanical Characteristics

- Material Type - UV stabilized PC+ABS, and polycarbonate, 94Vo rated
- RJ45 Jack Contact - Phosphor bronze, 50 $\mu$ , Gold Plating

#### Product Uses

Use for any unloaded keystone wall plate or patch panel.

#### Package Contents

- Cat5E keystone jack
- Two plastic strain relief caps for IDC connector
- Three color-coded designation dust covers with voice, data and Cat5E icons.

Order History  
Where To Buy  
More ▾

OEM Solutions  
Tech Support  
More ▾

ConnectXpress  
Drivers & Manuals  
More ▾

Call C2G **800.506.9607**



**United States** | Europe +

Copyright © 2019 C2G. All Rights Reserved

