



Part Number : [1300960040](#)

Product Description : Liquid-Tight Grip Strain Relief, 2" NPT, Straight Male, Mesh Length 0.19m (7.50")

Series Number : 130096

Status : Active

Product Category : Cable Grips

Engineering Part Number : 36375



Documents and Resources

Drawings

[1300960040 sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Cable Grips |
| Series | 130096 |
| Description | Liquid-Tight Grip Strain Relief, 2" NPT, Straight Male, Mesh Length 0.19m (7.50") |
| NEMA Rating | NEMA 4 |
| Product Name | Liquid-Tight |
| Type | Strain Relief Grip |
| UPC | 78678836375 |

Agency

| | |
|-----|---------|
| CSA | LR32159 |
| UL | E61303 |

Physical

| | |
|----------------------------|-----------------------------------|
| Approximate Break Strength | N/A |
| Bale Length | N/A |
| Body Style | Straight |
| Cable Diameter | N/A |
| Color - Grommet | N/A |
| Eye Type | N/A |
| Gender | Male |
| Material - Body | Malleable Iron, Zinc Plated Steel |
| Material - Grip | Stainless Steel |
| Mesh Length | 0.19m (7.50") |
| Net Weight | 0.001/kg |
| Number of Holes | N/A |
| O-Ring | N/A |

| | |
|-------------|--------|
| Thread Size | 2" NPT |
|-------------|--------|

This document was generated on May 27, 2026